



■ Specifications :

- Voltage rating: 200V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥100MΩ
- Contact resistance: ≤40mΩ
- After environmental testing : ≤80mΩ

X9862 T-P XX-A

- ① Series Number
- ② Category : T-terminal
- ③ Material:P-Phosphor bronze
- ④ Plating style:V01-Gold Flash;SN-Bright tin plating
- ⑤ Mold No./Mark/Special NO.A-Ultra-thin

X9862T-PSN-A	Phosphor Bronze	AWG#28-32	0.9mm(Max)	Stamping Before Pating:30u" Ni;70u"Sn Min	X9862H-A
PART NO	Material	Wire Range	Insulation O.D.	Finish	Suitable X K B

广东星坤科技股份有限公司
 文件工程章
 生效日期

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ANGLAR	±5°			
L ≤ 4	±0.2			
4 < L ≤ 16	±0.3			
16 < L ≤ 63	±0.4			
L > 63	±0.5			

DSND	DATE	SCALE: N/A	MODEL TYPE: X9862T-PXX-A
DWN	DATE	VIEW:	PART NO.: 1.25mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0