






NOTE:
 1.MATERIAL:
 HOUSING: THERMOPLASTIC HIGH TEMP WITH 40% GF, UL94V-0.
 CONTACT: BRASS T=0.20mm
 SHELL: STAINLESS T=0.50mm
 2.FINISH:
 CONTACT: GOLD PLATING ON CONTACT AREA,
 MATTE TIN PLATING ON SOLDER TAILS
 100u" MIN. NICKEL UNDERPLATING OVERALL.
 SHELL: 50-90u" NICKEL PLATING OVERALL.
 3. ▽ MAJOR DIMENSION ▽ CRITICAL DIMENSION



RECOMMENDED P.C.B LAYOUT (THICKNESS=1.2mm)
 (COMPONENT SIDE) TOLERANCES ±0.05mm



A71-05H7-1X1N1

1:AU 1U"
 5:AU 15U"
 6:AU 30U"

					DSND		DATE		SCALE: N/A	MODEL TYPE: HDMI CONNECTOR		
					ANGLAR		DATE		VIEW:	PART NO.:		
					$L \leq 4$		DATE		UNIT: mm/in	DWG NO.: A71-05H7-1X1N1		
					$4 < L \leq 16$		DATE		SIZE: A4			
					$16 < L \leq 63$		DATE					
					$L > 63$		DATE					
MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	XKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT 1.0g	SHEET 1/1	REVISION A0