





**Specifications :**

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤20mΩ
- After environmental testing : ≤30mΩ

X2581 T F-P SN  
① ② ③ ④ ⑤

- ① Series No.
- ② Category : T-Terminal
- ③ Shape:F-Female
- ④ Material: P-Phosphor bronze ;
- ⑤ Plating Style: SN-Bright Tin Plating (70u")



X2530TF-PSN	Phosphor Bronze	AWG#22-26	1.55mm(Mi.x)	Stamping Before Plating 30-50u" Ni,70-120u" Sn	X2530H
PART NO	Material	Wire Range	Insulation O. D.	Finish	Used In XKB Housing

广东星坤科技股份有限公司

生效	ΔX	日期
	ΔX	日期
	ΔX	日期
	MARK	DESCRIPTION

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X2530TF-PSN
DWN	DATE	VIEW:	PART NO.: 2.54mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn