



■ Specifications :

- Voltage rating: 200V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥100MΩ
- Contact resistance: ≤40mΩ
- After environmental testing : ≤50mΩ

X9862 H-XXA-N0

- ① Series No.
- ② Category : H-HSG
- ③ Row No.-Pin No.: XX-02P~30P
- ④ Plug the Pin&Special N0:A-Ultra-thin
- ⑤ Material : N0-PA66 94V-0

PIN	Dimensions(mm)				
	A	B	C	D	E
02	3.36	2.90	1.25	4.30	2.50
03	4.61	4.05	2.90	5.55	3.75
04	5.86	5.30	3.75	6.80	4.85
05	7.11	6.55	5.00	8.05	5.70
06	8.36	7.80	6.25	9.30	5.70
07	9.61	9.05	7.50	10.55	7.50
08	10.86	10.30	8.75	11.80	
09	12.11	11.55	10.00	13.05	
10	13.36	12.80	11.25	14.30	
11	14.61	14.05	12.50	15.55	
12	15.86	15.30	13.75	16.80	
13	17.11	16.55	15.00	18.05	
14	18.36	17.80	16.25	19.30	
15	19.61	19.05	17.50	20.55	
16	20.86	20.30	18.75	21.80	

X9862H-XXA-N0	PA66 UL 94V-0	X9862T	X9862W-A
PART NO	Material	Suitable X KB Terminal	Suitable X KB Terminal

广东星坤科技股份有限公司

生效

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	X9862H-XXA-N0
CHKD	DATE	UNIT: mm/in	PART NO.: 1.25mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn