



■ Specifications :

- Voltage rating: 50 V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥100MΩ
- Contact resistance: ≤20mΩ

X1011 WRS-2*XX-9T XX

- ① Series No.
- ② Category : W-WAFER
- ③ Wedding Board Angle : R-Right 90°
- ④ Welding Way:S-SMT
- ⑤ Row No.Pin No.2*02-2*25
- ⑥ Material:9T-PA9T 94V-0
- ⑦ Planting Category:SN-Bright tin plating
V01-All Gold Flash

Poles	Dimensuons(mm)		
	A	B	C
2*05	4.00	8.10	5.5
2*06	5.00	9.10	6.5
2*08	7.00	11.10	8.5
2*10	9.00	13.10	10.5
2*15	14.00	18.10	15.5
2*20	19.00	23.10	20.5
2*25	24.00	28.1	25.5

X1011WRS-2*XX-9TV01	PA9T UL 94V-0	Phosphor Bronze	Gold-Flash	X1011H
X1011WRS-2*XX-9TSN	PA9T UL 94V-0	Phosphor Bronze	TIN-Plated	
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Terminal

广东星坤科技股份有限公司

生效
日期
文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX				ANGLAR ±5°
ΔX				L ≤ 4 ±0.2
ΔX				4 < L ≤ 16 ±0.3
MARK				16 < L ≤ 63 ±0.4
				L > 63 ±0.5

DSND	DATE	SCALE: N/A	MODEL TYPE: X1011WRS-2*XX-9TV01
DWN	DATE	VIEW:	PART NO.: 1.0mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn