




■ Specifications :

- Voltage rating: 50 V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥100MΩ
- Contact resistance: ≤20mΩ

X1011 WWS-2*XX-9T XX

- ① Series No.
- ② Category : W-WAFER
- ③ Wedding Board Angle : V-Stright 90°
- ④ Welding Way:S-SMT
- ⑤ Row No.Pin No.2*02-2*25
- ⑥ Material:9T-PA9T 94V-0
- ⑦ Planting Category:SN-Bright tin plating
V01-All Gold Flash



Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
2*02	1.00	4.30	2.5	2*14	13.0	16.30	14.5
2*03	2.00	5.30	3.5	2*15	14.0	17.30	15.5
2*04	3.00	6.30	4.5	2*16	15.0	18.30	16.5
2*05	4.00	7.30	5.5	2*18	17.0	20.30	18.5
2*06	5.00	8.30	6.5	2*20	19.0	22.30	20.5
2*08	7.00	10.30	8.5	2*25	24.0	27.30	25.5
2*10	9.00	12.30	10.5				
2*11	10.00	13.30	11.5				
2*12	11.00	14.30	12.5				

X1011WWS-2*XX-9TV01	PA9T UL 94V-0	Phosphor Bronze	Gold-Flash	X1011H
X1011WWS-2*XX-9TSN	PA9T UL 94V-0	Phosphor Bronze	TIN-Plated	
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

ΔX	日期
ΔX	
ΔX	
MARK	DESCRIPTION

REVISIONS

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X1011WWS-2*XX-9TV01
DWN	DATE	VIEW:	PART NO.: 1.0mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

文件工程章