








PCB LAYOUT




0.1




2P



3P



5P



8P

Specifications:

规格:
 Voltage rating:125V AC/DC
 额定电压: 125V AC/DC
 Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage:500V AC/minute
 耐受电压: 500V AC/分钟
 Temperature range:-45°C~+105°C
 温度范围: -45°C~+105°C
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance:≤10mΩ
 接触电阻: ≤10mΩ
 After environmental testing:≤20mΩ
 环境测试后: ≤20兆欧

X2009 W RS-XX-9TSW

① ② ③ ④ ⑤ ⑥ ⑦

- Series No.
- Category:W-WAFER
- Welding Board Angle:R-Right Angle 90°
- Welding Way: S-SMT
- Row No-Pin No: XX-02P~15P
- Material: 9T-PA9T 94V-0
- Plating Category: SW-Fog Tin plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	c		A	B	C
2	2.00	8.00	4.80	9	16.00	22.00	18.80
3	4.00	10.00	6.80	10	18.00	24.00	20.80
4	6.00	12.00	8.80	11	20.00	26.00	22.80
5	8.00	14	10.80	12	22.00	28.00	24.80
6	10.00	16	12.80	13	24.00	30.00	26.80
7	12.00	18	14.80	14	26.00	32.00	28.80
8	14.00	20	16.80	15	28.00	34.00	30.80

X2009WRS-XX-9TSW	PA9T UL 94V-0	Brass	Tin-Plated	Brass	Tin-Plated	X2009H
PART NO	Material	Material(Pin)	Finish(Pin)	Material(Solder Tabs)	Finish(Solder Tabs)	Suitable XKB Terminal

广东星坤科技股份有限公司

生	日期						units: mm
效							tolerance:
ΔX							X.X ±0.2mm
ΔX							X.XX ±0.1mm
MARK							X.XXX ±0.05mm
文件工程章	DESCRIPTION	DATE	REVISED	APPROVED			UNSPECIFIED TOLERANCES
	REVISIONS						
	www.xk-dg.cn	www.helloxkb.com	www.helloxkb.cn				

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector
DWN		DATE		VIEW:	PART NO.: 2.00mm Crimp Style Connectors
CHKD		DATE		UNIT: mm/in	DWG NO.: X2009WRS-XX-9TSW
APPD		DATE		SIZE: A4	WEIGHT SHEET REVISION 1.0g 1/1 A0
KKB INDUSTRIAL PRECISION CO., LIMITED					