



Specifications:

规格:
 Voltage rating:125V AC/DC
 额定电压: 125V AC/DC
 Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage:500V AC/minute
 耐受电压: 500V AC/分钟
 Temperature range:-45°C-+105°C
 温度范围: -45°C-+105°C
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance:≤10mΩ
 接触电阻: ≤10mΩ
 After environmental testing:≤20mΩ
 环境测试后: ≤20兆欧



X2009 W V S-XX-9TSW

① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No.
- 2.Category:W-WAFER
- 3.Welding Board Angle:V-Straight 180°
- 4.Welding Way: S-SMT
- 5.Row No-Pin No: XX-02P~15P
- 6.Material: 9T-PA9T 94V-0
- 7.Plating Category: SW-Fog Tin plating



Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	c		A	B	C
2	2.00	10.90	4.80	9	16.00	24.60	18.80
3	4.00	12.60	6.80	10	18.00	26.60	20.80
4	6.00	14.60	8.80	11	20.00	28.60	22.80
5	8.00	16.60	10.80	12	22.00	30.60	24.80
6	10.00	18.60	12.80	13	24.00	32.60	26.80
7	12.00	20.60	14.80	14	26.00	34.60	28.80
8	14.00	22.60	16.80	15	28.00	36.60	30.80



XKB:7.80[0.307]

X2009WVS-XX-9TSW	PA9T UL 94V-0	Brass	Tin-Plated	Brass	Tin-Plated	X2009H
PART NO	Material	Material(Pin)	Finish(Pin)	Material(Solder Tabs)	Finish(Solder Tabs)	Suitable XKB Terminal

广东星坤科技股份有限公司

生	日期
效	
文件	工程
MARK	章

DSND	DATE	SCALE: N/A	MODEL TYPE: Wire to board connector
DWN	DATE	VIEW:	PART NO.: 2.00mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.: X2009WVS-XX-9TSW
APPD	DATE	SIZE: A4	WEIGHT 1.0g
KKB INDUSTRIAL PRECISION CO., LIMITED			SHEET 1/1
			REVISION A0

units: mm
 tolerance:
 X.X ±0.2mm
 X.XX ±0.1mm
 X.XXX ±0.05mm
 UNSPECIFIED TOLERANCES

DESCRIPTION

REVISIONS

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn