



**PCB LAYOUT**

**Specifications:**

规格:  
**Voltage rating:** 250V AC/DC  
**额定电压:** 250V AC/DC  
**Current rating:** 2A AC/DC  
**额定电流:** 2A AC/DC  
**Withstanding voltage:** 1500V AC/minute  
**耐压电压:** 1500V AC/分钟  
**Temperature range:** -25°C ~ +85°C  
**温度范围:** -25°C ~ +85°C  
**Insulation resistance:** ≥1000MΩ  
**绝缘电阻:** ≥1000MΩ  
**Contact resistance:** ≤20mΩ  
**接触电阻:** ≤20mΩ  
**Line type:** AWG#22 AWG#24 AWG#26 AWG#28  
**线型:** AWG#22 AWG#24 AWG#26 AWG#28

**X9254 W V X - XX X -N0 SN XX**

- ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨
- ① Series No.
  - ② Category: W-WAFER
  - ③ Welding Board Angle: V-Stright 180°
  - ④ Welding Way: Blank-DIP
  - ⑤ Row No.-Pin No.: XX-02~16P
  - ⑥ Plug the Pin & Special No.
  - ⑦ Material: N0 -PA66 94V-0
  - ⑧ Plating Category: SN-Bright Tin Plating
  - ⑨ Color : Blank-Natural Color

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	2.54	5.08	10	22.86	25.40
3	5.08	7.62	11	25.40	27.94
4	7.62	10.16	12	27.94	30.48
5	10.16	12.70	13	30.48	33.02
6	12.70	15.24	14	33.02	35.56
7	15.24	17.78	15	35.56	73.66
8	17.78	20.32	30	73.66	76.20
9	20.32	22.86			

X9254WV-XX-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X9254H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	PART NO.: 2.54mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	X9254WV-XX-N0SN
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0

广东星坤科技股份有限公司

生 日期  
 發 日期

文件工程章  
 REVISIONS: DATE REVISED APPROVED UNSPECIFIED TOLERANCES