




SECTION: A-A  
SCALE: 1:1



SECTION: B-B  
SCALE: 1:1



电镀后收料方向示意图  
(压线开口朝外)

Specifications(规格):  
 Voltage rating(额定电压):500V AC/DC  
 Current rating(额定电流):2A AC/DC  
 Withstanding voltage(耐压值):1500V AC/minute  
 Temperature range(工作温度):-40℃~+85℃  
 Insulation resistance(绝缘电阻):1000MΩ  
 Contact resistance(接触电阻):<30mΩ  
 After environmental testing(环境测试后):≤40mΩ

X3700T X-P SN X-X  
 $\odot \odot \odot \odot \odot \odot \odot \odot \odot \odot$

- ① 系列
- ② 类别: T-端子
- ③ 外观形态: 空码-普通脚
- ④ 材质: P-磷铜
- ⑤ 电镀类别: G\*\*-镀金 V\*\*-镀全金  
 \*01-Gold Flash \*02-2u" \*03-3u" \*05-5u"  
 \*10-10u" \*15-15u" \*30-30u" \*50-50u"  
 SN-镀亮锡(70-120u") SN1-镀亮锡(120u"/Min.)  
 0-素材 SW-镀雾锡
- ⑥ 电镀方式: 空码-先冲后镀
- ⑦ 模号/MARK及特殊码:

X3700T-PSN	Phosphor Bronze	AWG 28-32	0.7mm(Max)	Stamping Before Plating 30u"	X3700H
PART NO	Material	Wire Range	Insulation O.D	Finish	Suitable Xi/B Terminal

广东星坤科技股份有限公司

生	日期
发	
Δ	
文件工程章	

REVISIONS

DATE	REVISED	APPROVED

UNSPECIFIED TOLERANCES

www.xkpcb.com www.hellixkb.cn

DSND	DATE	SCALE: N/A	MODEL TYPE: X3700T-PSN
DWNN	DATE	VIEW:	PART NO.: 3.70mm BTB Style Connectors
CHKD	DATE	UNIT: mm/mIn	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0