



Recommended P.C.B Layout

General Tolerance: ±0.05

Specifications:

规格:
Voltage rating: 30V AC/DC
额定电压: 30V AC/DC
Current rating: 0.2A AC/DC
额定电流: 0.2A AC/DC
Withstanding voltage: 200V AC/分钟
耐压电压: 200V AC/分钟
Temperature range: -25°C ~ +85°C
温度范围: -25°C ~ +85°C
Insulation resistance: ≥100MΩ
绝缘电阻: ≥100MΩ
Contact resistance: ≤30mΩ
接触电阻: ≤30mΩ

X0600 W R S - XX - LP V01 HF

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No.
- ② Category: W-wafer
- ③ Welding Board Angle: R-90°
- ④ Row No.-Pin No.: XX-Single row
- ⑤ Material: LP-LCP 94V-0
- ⑥ Planting Category : V01-All Gold Flash
- ⑦ Plug the Pin & Special NO. HF-Halogen Free

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	0.60	3.00	12	6.60	9.00
3	1.20	3.60	13	7.20	9.60
4	1.80	4.20	14	7.80	10.20
5	2.40	4.80	15	8.40	10.80
6	3.00	5.40	16	9.00	11.40
7	3.60	6.00	17	9.60	12.00
8	4.20	6.60	18	10.20	12.60
9	4.80	7.20	19	10.80	13.20
10	5.40	7.80	20	11.40	13.80
11	6.00	8.40	22	12.60	15.00

X0600WRS-XX-LPV01HF	LCP UL 94V-0 (Halogen Free)	Phosphor Bronze	Gold-Flash	Brass	Gold-Flash	X0600H
PART NO	Material	Material(Pin)	Finish(Pin)	Material (Solder Tabs)	Finish (Solder Tabs)	Suitable XKB Terminal

广东星坤科技股份有限公司

生	日期
發	
Δ	
文件工程章	
REVISIONS	DATE
www.xkpcb.com	www.helixkb.com
www.helixkb.com	www.helixkb.com

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: NA	MODEL TYPE:
DWNN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	X0600WRS-XX-LPV01HF
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT
			1.0g
			SHEET
			1/1
			REVISION
			A0