



■ Specifications :

- Voltage rating: 50 V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 100M\Omega$
- Contact resistance: $\leq 30m\Omega$
- After environmental testing : $\leq 50m\Omega$


X1251 T-P SN

① ② ③ ④


- ① Series Number.
- ② Category : T-terminal
- ③ Material : P-Phosphor bronze
- ④ Plating style:V01-Gold Flash;SN-Bright tin plating



SECTION:A-A
SCALE:1:1



SECTION:B-B
SCALE:1:1



SECTION:C-C
SCALE:1:1

X1251T-PV01	Phosphor Bronze	AWG#26-30	1.00mm(Max)	Stamping Before Pating:30u" Ni MIN; Whole Gold:Gold Flash	X1251H
X1251T-PSN	Phosphor Bronze	AWG#26-30	1.00mm(Max)	Stamping Before Pating:30u" Ni MIN;70u"Sn MIN	
PART NO	Material	Wire Range	Insulation O.D	Finish	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

REVISIONS

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

ANGLAR	$\pm 5^\circ$
$L \leq 4$	± 0.2
$4 < L \leq 16$	± 0.3
$16 < L \leq 63$	± 0.4
$L > 63$	± 0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X1251T-PSN
DWN	DATE	VIEW:	PART NO.: 1.25mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

文件工程章