


2x01P 2x02P 2x03P 2x04P



2x05P 2x06P

Specifications :

Voltage rating: 600V AC / DC
 Current rating: 23A AC / DC
 Withstanding voltage: 2200V AC/minute
 Temperature range: -40°C~+105°C
 Insulation resistance: ≥1000M Ω
 Contact resistance: ≤2mΩ
 After environmental testing : ≤10m Ω

X5700 H -2xXX-N0

① ② ③ ④

- ① Series No.
- ② Category : H-HSG
- ③ Row No.-Pin No.: 2xXX-2x01P~2x06P
- ④ Material : N0-PA66 94V-0

Poles	Dimensions (mm)	
	A	
2x01	8.35	
2x02	12.05	
2x03	17.75	
2x04	23.45	
2x05	29.15	
2x06	34.85	

X5700H-2xXX-N0	Nylon 66 UL 94V-0	X5700T	X5700W
PAPT NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

生 日期
 ΔX 效
 ΔX 日期
 ΔX 文件工程章
 MARK REVISIONS
 www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

units:	mm
tolerance:	
X.X	±0.2mm
X.XX	±0.1mm
X.XXX	±0.05mm
UNSPECIFIED TOLERANCES	

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	DWG NO.:
APPD		DATE		SIZE: A4	X5700H-2xXX-N0
XKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET
				1.0g	1/1
				REVISION	A0