

Specifications:

Voltage rating:30V AC/DC

Current rating:0.5 A AC/DC


Withstanding voltage: 500V AC/minute

Temperature range:-30° ~+70


Insulation resistance:≥100MΩ

Contact resistance: ≤30mΩ

After environmental testing:≤20mΩ



P.C.B LAYOUT TOP VIEW



	MATERIAL	PLATING
terminal 1	Phosphor Bronze	AG
terminal 2	Phosphor Bronze	AG
terminal 3	Phosphor Bronze	AG
plastic	PAA	

						DSND		DATE		SCALE: N/A	MODEL TYPE: 2.5 PHONE JACK		
Δx						DWN		DATE		VIEW:	PART NO.:		
Δx						CHKD		DATE		UNIT: mm/in	DWG NO.:		
Δx						APPD		DATE		SIZE: A4	PJ-208		
MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
											1.0g	1/1	A0