





■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10mΩ
- After environmental testing : ≤20mΩ

X2564 T P- SN
① ② ③ ④

- ① Series Number.
- ② Category : Terminal
- ③ Material:P-Phosphor bronze
- ④ Plating style:SN-Bright tin Plating



X2564T-BSN	Brass				
X2564T-BSNB				Stamping Before Plating 30U' Ni/70U'sn	
X2564T-PSNB	Phosphor Bronze	AWG#22-28	1.90mm(Max)		X2564H
X2564T-PSN					
PART NO	Material	Wire Range	Insulation O.D.	Finish	Suitable X K B Terminal

SECTION: A-A
SCALE: 1:1

SECTION: B-B
SCALE: 1:1

广东星坤科技股份有限公司

生效	ΔX	日期
	ΔX	
	ΔX	
	MARK	DESCRIPTION

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X2564T-PSN
DWN	DATE	VIEW:	PART NO.: 2.5mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.: X2564T-PSN
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn