

The Main Thchnology Performance

主要技术性能

Rate vltage.current:50mA DC 12V

额定电压.电流: 50mA DC 12V

Contact resistance:≤100mΩ

接触电阻: ≤100mΩ

Operating force: 260±50gf

操作力: 260±50gf

Travel: 0.20±0.1mm

行程: 0.20±0.1mm

Insulated resistance: ≥100mΩ



绝缘电阻: ≥100mΩ

Dielectric strength: ≥250VAC/lmin


绝缘电强度: ≥250VAC/lmin

Endurance: ≥30000

耐力: ≥30000



PCB.WELDING DRAWING



CIRCUIT DIAGRAM

ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR
D	Yellow membrane	polyimide	1	Orange
C	Shrapnel	SUS	2	plate with silver
B	Clasp	phosphorous copper	1	plate with solver
A	Pedestal	LCP	1	grey

广东星坤科技股份有限公司

B

生	日期
效	
文件	工程
章	

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.: TS-1177A-C
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET 1/1
			REVISION A0