



X1002H-XXB1-N0	PA66 uL 94V-O	1002T-A	1002W
X1002H-XXB1-NOHF	PA66 UL 94V-0 Halogen Free	1002T-A	1002W
PART NO	Material	Suitable XKB Terminal	Suitable XKB

X1002 H - XX B1- N0 XX HF

- ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category: H-HSG
- ③ Row No.-Pin No.: XX-02P-20P
- ④ Row No.-Pin No.: XX-Single Row
- ⑤ Plug the Pin & special No.: B-Ultra-thin hook
- ⑥ Material : NO-PA66 94V-0
- ⑦ Color: Blank-Natural Color
HF-Halogen Free

Specifications:

规格:
 Voltage rating: 125V AC/DC
 额定电压: 125V AC/DC
 Current rating: 1A AC / DC
 额定电流: 1A AC / DC
 Withstanding voltage: 500V AC/minute
 耐压电压: 500V AC/minute
 Temperature range:-25℃~+85℃
 温度范围: -25℃~+85℃
 Insulation resistance: ≥100MΩ
 绝缘电阻: ≥100MΩ
 Contact resistance: ≤20mΩ
 接触电阻: ≤20mΩ
 After environmental testing: ≤40mΩ
 环境测试后: ≤40mΩ

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
2	1.00	3.00	2.40	12	11.00	13.00	12.40
3	2.00	4.00	3.40	13	12.00	14.00	13.40
4	3.00	5.00	4.40	14	13.00	15.00	14.40
5	4.00	6.00	5.40	15	14.00	16.00	15.40
6	5.00	7.00	6.40	16	15.00	17.00	16.40
7	6.00	8.00	7.40	17	16.00	18.00	17.40
8	7.00	9.00	8.40	18	17.00	19.00	18.40
9	8.00	10.00	9.40	19	18.00	20.00	19.40
10	9.00	11.00	10.40	20	19.00	21.00	20.40
11	10.00	12.00	11.40				

广东星坤科技股份有限公司

生
發

日
期

文件工程章

REVISIONS

www.xkb.com www.helixkb.com www.helixkb.cn

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: NA	MODEL TYPE:
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	1.00 mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
			X1002H-XXB1-NOHF
XKB INDUSTRIAL PRECISION CO., LIMITED		WEIGHT	SHEET
		1.0g	1/1
			REVISION
			A0