



■ Specifications :

- Voltage rating: 50 V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥100MΩ
- Contact resistance: ≤20mΩ

X1011 H-2*XX- N0 HF
 ① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category : H-HSG
- ③ Row No.Pin No.2*02-2*25
- ④ Material:N0-PA66 94V-0
- ⑤ HF-Halogen free

Poles	Dimensions(mm)		
	A	B	C
2*05	4.00	6.20	8.00
2*08	7.00	9.20	11.00
2*10	9.00	11.20	13.00
2*15	14.00	16.20	18.00
2*20	19.00	21.20	23.00
2*25	24.00	26.20	28.00

X1011H-2*XX-N0HF	PA66 UL 94V-0 Halogen Free	X1011T	X1011W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

生	日期
效	
文件工程章	
REVISIONS	

www.xk-ug.cn www.helloxkb.com www.helloxkb.cn

DATE	REVISED	APPROVED	ANGLAR	±5°
			L ≤ 4	±0.2
			4 < L ≤ 16	±0.3
			16 < L ≤ 63	±0.4
			L > 63	±0.5
UNSPECIFIED TOLERANCES				

DSND	DATE	SCALE: N/A	MODEL TYPE: X1011H-2*XX-N0HF
DWN	DATE	VIEW:	PART NO.: 1.0mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0