



Recommended P.C. Board Layout

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
香港星坤工業精密有限公司

Specifications :

- Voltage rating: 500V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -40°C~+105°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤20mΩ
- After environmental testing: ≤30mΩ

X9127 W V X - XX A4 - XX SN XX
 ①② ③④ ⑤⑥ ⑦⑧ ⑨

- ① Series No.
- ② Category: W-wafer
- ③ Welding Board Angle: V-180°
- ④ Welding Way: Blank-DIP
- ⑤ Row No.-Pin No. XX-Single row
- ⑥ Plug the Pin & Special NO.
 A4-Lack of on both sides,
 with the stay column
- ⑦ Material: 9T-PA9T UL94V-0; PT-PBT 94V-0
- ⑧ Planting Category: SN-Bright tin plating
- ⑨ Color: RE-red RD-purplish red

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A			A	
04	2.54		16	17.78	
06	5.08		18	20.32	
08	7.62		20	22.86	
10	10.16		22	25.40	
12	12.7		24	27.94	
14	15.24		26	30.48	

X9127WV-XXA4-PTSNRE	Red	PBT UL 94V-0	Brass	Tin-Plated
X9127WV-XXA4-9TSNRD	Purplish red	PA9T UL 94V-0		
X9127WV-XXA4-9TSNRE	Red	PA9T UL 94V-0		
PART NO	Color	Material	Material(Pin)	Finish(Pin)

DSND		DATE		SCALE: N/A	MODEL TYPE: X9127WV-XXA4-XXSNXX	
DWN		DATE		VIEW:	PART NO.:	
CHKD		DATE		UNIT: mm	1.27 mm Crimp Style Connector	
APPD		DATE		SIZE: A4	DWG NO.:	
				WEIGHT	SHEET	REVISION
				1.0g	1/1	A0

REVISIONS
 Authorized Signature(s)

XKB INDUSTRIAL PRECISION CO., LIMITED

F

F