


Specifications:

- 规格: XKB
Voltage rating: 150V AC/DC
 额定电压: 150V AC/DC
Current rating: 1A AC/DC
 额定电流: 1A AC/DC
Withstanding voltage: 500V AC/minute
 耐受电压: 500V AC/分钟
Temperature range: -25°C +85°C
 温度范围: -25°C +85°C
Insulation resistance: ≥500MΩ
 绝缘电阻: ≥500MΩ
Contact resistance: ≤30mΩ
 接触电阻: ≤30mΩ
After environmental testifg: ≤40兆欧
 环境测试后: ≤40兆欧

X9812 T X-P XX X-L
 ○ ○ ○ ○ ○ ○ ○ ○ ○ ○

- 01 Series No.
- 02 Category/T-terminal
- 03 Shape/Blank-ordinary
- 04 Material/P-Phosphor bronze
- 05 Plating style/V01-Gold Flash; SN-Brigt tin plating;
- 06 Plating method/Blank-Stamping before plating
- 07 Mold No./Mark/Special No. -Lose



XKB Connectivity

X9812T-PV01-L	Phosphor Bronze	AWG#26-30	1.00mm(Max)	Stamping Before Plating 30u" Ni/Whole Gold Gold Flash	X9812H
X9812T-PSN-L				Stamping Before Plating 30u" Ni/70u"Sn Min	
PART NO	Material	Wire Range	Insulation O.D	Finish	Suitable XKB Terminal

SECTION:A-A
SCALE:1:1

SECTION:B-B
SCALE:1:1

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS
 DATE REVISED APPROVED
 www.xkb.com www.hellxkb.com

UNSPECIFIED TOLERANCES

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

DSND	DATE	SCALE: N/A	MODEL TYPE: X9812T-PSN-L
DWNN	DATE	VIEW: ①	PART NO.: 1.25mm Crimp Style Connector
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g SHEET 1/1 REVISION A0