


C向



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating: 3A AC / DC

额定电流: 3A AC / DC

Withstanding voltage: 1000V AC/minute

耐压电压: 1000V AC/minute

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ


Contact resistance: ≤10Ω

接触电阻:≤10Ω


After environmental testing:≤20mΩ

环境测试后: ≤20mΩ

A-A



B-B



X2510 T-P SN

① ② ③ ④

① Series Number.

② Category:

③ Material:

④ Planting style

T-terminal

P-Phosphor bronze

SN-Bright tin plating

X2510T-PSN	Brass	AWG#22-28	1.57mm (Max)	Stamping Before Plating:30u" Ni;70u"Sn	X2510H
PART NO	Material	Wire Range	Insulation O.D.	Finish	Mates With XKB Housing

广东星坤科技股份有限公司

生
發

日
期

文件工程章

REVISIONS

www.xkb.com www.hellixkb.com www.hellixkb.cn

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	PART NO.: 2.54 mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	X2510T-BSNX
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0