



Specifications:

规格: XKB

Voltage rating: 150V AC/DC

额定电压: 150V AC/DC

Current rating: 1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage: 500V AC/minute

耐受电压: 500V AC/分钟

Temperature range: -25°C~+85°C

温度范围: -25°C~+85°C

Insulation resistance: ≥500MΩ

绝缘电阻: ≥500MΩ

Contact resistance: ≤30mΩ

接触电阻: ≤30mΩ

After environmental testing: ≤40mΩ

环境测试后: ≤40兆欧

X9812 W V S-2*XX X-XX V01 XX

- 01 Series No
- 02 Category: W-wafer
- 03 Welding Board Angle: V-Straight 18°
- 04 Welding Way: S-SMT
- 05 Row No.-Pin No: 2*xx-2*05P-2*25P
- 06 Plug the Pin&Special NO.: F-HF
- 07 Material:
 - 6T-PA6T 94V-0 9T-PA9T 94V-0
 - 1T-PA10T 94V-0
- 08 Planting Category: V01-Gold Flash
- 09 Color: Blank-Natural Color

Poles	Dimensions(mm)			
	A	B	C	D
2*05	5.00	12.50	8.15	7.50
2*06	6.25	13.75	9.40	8.75
2*07	7.50	15.00	10.65	10.00
2*10	11.25	18.75	14.40	13.75
2*12	13.75	21.25	16.90	16.25
2*15	17.50	25.00	20.65	20.00
2*20	23.75	31.25	26.90	26.25
2*25	30.00	37.50	33.15	32.50

X9812WVS-2*XX-1TV01	PA10T UL94V-0	Brass	Gold+Flash	X9812H		
X9812WVS-2*XX-6TV01	PA6T UL94V-0					
X9812WVS-2*XX-9TV01	PA9T UL94V-0					
PART NO	Material (Water And Cap)	Material (Pin And Solder Tabs)	Finish (Pin And Solder Tabs)	Suitable XKB Terminal		
DSND	DATE	SCALE: N/A	MODEL TYPE:			
DWNN	DATE	VIEW:	X9821WVS-2*XX-XXV01			
CHKD	DATE	UNIT: mm/in	PART NO.:	2.40mm Crimp Style Connectors		
APPD	DATE	SIZE: A4	DWG NO.:			
XKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET	REVISION
				1.0g	1/1	A0

广东星坤科技股份有限公司
General Manager: 05

生 日期

文件工程章

REVISIONS
www.helxkb.com

UNSPECIFIED TOLERANCES

XKB	ANGLR	±5°
	L ≤ 4	±0.2
	4 < L ≤ 16	±0.3
	16 < L ≤ 63	±0.4
	L > 63	±0.5