



■ Specifications :

- Voltage rating: 125V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 250V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance:  $\geq 100M\Omega$
- Contact resistance:  $\leq 20m\Omega$
- After environmental testing :  $\leq 40m\Omega$

X9821 T M -P -XX

- ① Series Number
- ② Category : T-terminal
- ③ Welding Board Angle : M-Male
- ④ Material:P-Phosphor bronze
- ⑤ Plating style:V01-Gold Flash;SN-Bright tin plating  
SN2-Bright Tin Plating 120u"Min

X9821TM-PN2				Stamping Before Plating:50u" Min Ni;120u"Sn Min	
X9821TM-PV01	Phosphor Bronze	AWG#28-32	1.0mm(Max)	Stamping Before Plating:30u" Min Ni;Whole Gold:Gold Flash	X9821HF-PSN
X9821TM-PSN				Stamping Before Plating:30u" Min Ni;70u"Sn Min	
PART NO	Material	Wire Range	Insulation O.D	Finish	Suitable X K B

广东星坤科技股份有限公司

生效

$\Delta X$		日期
$\Delta X$		日期
$\Delta X$		日期
MARK	DESCRIPTION	

REVISIONS

UNSPECIFIED TOLERANCES

DSND		DATE		SCALE: N/A	MODEL TYPE: X9821TM-PXX
DWN		DATE		VIEW:	PART NO.: 1.25mm Crimp Style Connectors
CHKD		DATE		UNIT: mm/in	DWG NO.:
APPD		DATE		SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET
				1.0g	1/1
				REVISION	A0

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn