



Circuit Diagram □:Terminal No.


Matching Plug



| CODE | PLATING |
|------|---|
| -B | Bushing&Nut (Ni Plated) Terminal (Ag Plated) |
| -D | Bushing&Nut (Ni Plated) Terminal (Au Plated) |
| -F | Bushing&Nut (Au Plated) Terminal (Au Plated) |

Specification:

- 1.Rating: DC 30V 0.5A.
- 2.Contact resistance: ≤30mΩ
After test: ≤50mΩ.
- 3.Insulation resistance:≥100mΩ (500VDC).
After test:≥50mΩ.
- 4.Withstanding voltage:500vac.
- 5.Insertion and extraction force:3N~30N.
- 6.life test:5000cycles min.
- 7.Operation temperature range:-20℃+70℃.
- 8.Preservative temperature range:-40℃+85℃.
- 9.Significance dimension.



| | MATERIAL | PLATING |
|------------|-----------------|---------|
| terminal 1 | Phosphor Bronze | tin |
| terminal 2 | Phosphor Bronze | tin |
| terminal 3 | Phosphor Bronze | tin |
| plastic | Pbt | |

广东星坤科技股份有限公司

| | |
|----|----|
| 生 | 日期 |
| 效 | 日期 |
| 文件 | 工程 |

| | | | |
|--------------------------------------|------|-------------|-------------------------------|
| DSND | DATE | SCALE: N/A | MODEL TYPE: 3.5 PHONE JACK |
| DWN | DATE | VIEW: | PART NO.: |
| CHKD | DATE | UNIT: mm/in | DWG NO.: PJ-392W-X |
| APPD | DATE | SIZE: A4 | WEIGHT 1.0g |
| UNSPECIFIED TOLERANCES | | | SHEET 1/1 |
| XKB INDUSTRIAL PRECISION CO.,LIMITED | | | REVISION A0 |