



PCB LAND DIMENSION

SPECIFICATION

Contact Rating: 50mA, 12V DC  
 Contact Resistance: 100mΩ max  
 Insulation Resistance: 100mΩ min.500V DC  
 Dielectric Strength: 250V AC/1minute  
 Operating Temp: -30°C~+85°C  
 Storage Temp: -30°C~+80°C  
 Operating Temp: 100,000cycles

PAPT NO	TS-1186F-X-X
Operating Force	B:160gf C:260gf
Height	H:3.6
Fixed column	A:With B:Without

ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Cover	—	1	SUS		
④	Keystake	—	1	Pa46	Black	
③	Contact	—	1	F.ag/Sus		
②	Housing	—	1	LCP	Black	
①	Terminal	—	1	Brass (0.30t)	Plating silvering	

DSND	DATE	SCALE: N/A	MODEL TYPE: TACT SWITCH
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	TS-1186F-X-X
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

units: mm				
tolerance:				
X.X	±0.2mm			
X.XX	±0.1mm			
X.XXX	±0.05mm			
UNSPECIFIED TOLERANCES				
MARK	DESCRIPTION	DATE	REVISED	APPROVED
REVISIONS				
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn				