

1X6PIN



1X8PIN



1X7PIN



1X9PIN




1X5PIN



1X10PIN



1X4PIN



1X11PIN



1X3PIN



1X12PIN




1X2PIN

### Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -40°C~+105°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10m Ω
- After environmental testing : ≤20m Ω

X3025 H F-XX XX-N2 XX



- ① Series No.
- ② Category : H-HSG
- ③ Welding Board Angle : F-Female HSG
- ④ Row No.-Pin No. : XX-02P-12P
- ⑤ Plug the Pin & special No. : I-Without Ears  
G-With Ears
- ⑥ Material : N2-PA66 94 V-2;
- ⑦ Color : Blank-Natural Color ; WH-White

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	3.00	6.90	08	21.00	24.90
03	6.00	9.90	09	24.00	27.90
04	9.00	12.90	10	27.00	30.90
05	12.00	15.90	11	30.00	33.90
06	15.00	18.90	12	33.00	36.90
07	18.00	21.90			

PART NO	Material	Color	Suitable XXB Terminal	Mates With XXB Housing	Note
X3025H-XXQ-N2	Nylon 66 94V-2	Natural Color			
X3025HF-XXQ-N2WH	Nylon 66 94V-2	White		X3025TM	X3025HM With Ears
X3025HF-XXI-N2	Nylon 66 94V-2	Natural Color		X3025TM	X3025HM Without Ears
X3025HF-XXI-N2WH	Nylon 66 94V-2	White		X3025TM	X3025HM Without Ears

广东星坤科技股份有限公司

生 日期  
發 日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: NA	MODEL TYPE: X3025HF-XXX-N2
DWNN	DATE	VIEW: ④	PART NO.: 3.00mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g SHEET 1/1 REVISION A0