



XKB



Specifications:
 规格: **XKB**
 Voltage rating: 600V AC/DC
 额定电压: 600V AC/DC
 Current rating: 9A AC/DC
 额定电流: 9A AC/DC
 Withstanding voltage: 1500V AC/minute
 耐受电压: 1500V AC/分钟
 Temperature range: -25°C +85°C
 温度范围: -25°C +85°C
 Insulation resistance: ≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance: ≤10mΩ
 接触电阻: ≤10mΩ XKB
 After environmental testing: ≤20兆欧
 环境测试后: ≤20兆欧

X9357TF-XSN X-H
 ① ② ③ ④ ⑤ ⑥ ⑦
 01 Series Number
 02 Category: T-terminal
 03 Shape: F-Female
 04 Material: B-Brass; P-Phosphor Bronze
 05 Plating style: SN-Bright tin plating
 06 Plating method:
 Blank-Stamping before plating;
 07 Special No: H-High Leads

X9357TF-PSN-H	Phosphor Bronze	AWG#16-24	3.10mm(Max)	Stamping Before Plating :30u" MIN. Ni70u"Sn MIN.	X9357HM
X9357TF-BSN-H	Brass				
PART NO	Material	Wire Range	Insulation O.D	Finish	Suitable XKB

广东星坤科技股份有限公司

生 日期

文件工程章

XKB				DSND	DATE	SCALE: NA	MODEL TYPE: X9357TF-XSN-H	
XKB	ANGLAR	±5°	DWN	DATE	VIEW:	PART NO.: 2.40mm Crimp Style Connectors		
	L ≤ 4	±0.2	CHKD	DATE	UNIT: mm/in	DWG NO.:		
	4 < L ≤ 16	±0.3	APPD	DATE	SIZE: A4			
	16 < L ≤ 63	±0.4	UNSPECIFIED TOLERANCES					
	L > 63	±0.5	XKB INDUSTRIAL PRECISION CO., LIMITED					WEIGHT 1.0g
REVISIONS	DATE	REVISED	APPROVED				SHEET 1/1	
www.helxkb.com							REVISION A0	