





Material
 Housing Material: LCP, UL94V-0, black
 Contact Terminal: Copper Alloy
 Metallic Shell: Sus
 Electrical
 Voltage Rating: 30 V AC
 Current Rating: Signal (Pins 2,3,4): 1.0A, Power (Pins 1,5): 1.8A
 Contact Resistance: 30mΩ Max
 Insulation resistance: 1000MΩ Min
 Dielectric withstanding voltage: 250V AC/Minute
 Mechanical
 Durability: 10,000 cycles
 Mating Force: 35N (3.57Kgf) Max
 Unmating Force: 8N (0.82Kgf) Min.



U254-05XX-4BH83-XXS
 1:AU 1U"
 6:AU 30U"
 T:TIN
 N:NICKEL
 L:S:Sus
 1:With 2:Without
 S:Scrolls F:Flat

RECOMMENDED P.C.B. LAYOUT
 TOP VIEW (TOLERANCE: ±0.05)

ANGLR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: NA	MODEL TYPE: MICRO USB
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	U254-05XX-4BH83-SXS
		WEIGHT	SHEET
		1.0g	1/1
		REVISION	A0

广东星坤科技股份有限公司

生 日期
 發 日期

文件工程章
 日期 日期 日期 日期
 日期 日期 日期 日期

REVISIONS
 www.xkpcb.com www.hellixkb.com

XKB INDUSTRIAL PRECISION CO., LIMITED