



SPECIFICATIONS
 Current Rating: 1.5A AC, DC
 Voltage Rating: 50V AC, DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 20mΩ Max.
 Insulation Resistance: 100MΩ Min.
 Withstanding Voltage: 500V AC/minute
 Material: Phosphor Bronze

X1224 T- P V01
 ① ② ③ ④

- ① Series No.
- ② Category : T-terminal
- ③ Material: P-Phosphor bronze
- ④ Plating Style:
V01-All Gold Flash

X1224T-PV01	Phospho Bronze	AWG#28-30	0.70mm	Stamping Before Pating: 30u" Ni; Whole Gold: Gold Flash	X1224H
PART No	Material	Wire Range	Insulation O.D.	Finish	Suitable XKB Terminal

						ANGLAR	±5°	
Δx						L ≤ 4	±0.2	
Δx						4 < L ≤ 16	±0.3	
Δx						16 < L ≤ 63	±0.4	
MARK						L > 63	±0.5	
REVISIONS							UNSPECIFIED TOLERANCES	
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn								

DSND		DATE		SCALE: N/A	MODEL TYPE: X1224T-PV01	
DWN		DATE		VIEW:	PART NO.: 1.20mm Crimp Style Connectors	
CHKD		DATE		UNIT: mm/in	DWG NO.:	
APPD		DATE		SIZE: A4		
XKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET	REVISION
				1.0g	1/1	A0