



Specifications:

规格:
Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
Current rating:3A AC/DC
 额定电流: 3A AC/DC
Withstanding voltage:600V AC/minute
 耐受电压:600V AC/分钟
Temperature range:-25℃~+85℃
 温度范围: -25℃~+85℃
Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
Contact resistance:≤20mΩ
 接触电阻: ≤20mΩ
After environmental testing:≤30mΩ
 环境测试后: ≤30兆欧
Operating Temperature:-40℃ to +105℃
 工作温度: -40℃至? 105℃

X9555 W V X-2xXX A-PT V01 XX

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1. Series No
2. Category:W-WAFER
3. Welding Board Angle:V-Straight 180°
4. Welding Way:Blank-DIP
5. Row No-Pin No:2xXX-2x06P-2x64P
6. Plug the Pin&Special NO:A-Ejector Header
7. Material:PT-PBT 94V-0
8. Plating Category:V01-All Gold Flash
9. Color:Blank-Natural Color

poles	Dimensions(mm)		poles	Dimensions(mm)	
	A	B		A	B
2x06	5.08	26.82	2x26	30.48	52.22
2x08	7.62	29.36	2x30	35.56	57.30
2x10	10.16	31.90	2x34	40.64	62.38
2x14	15.24	36.98	2x40	48.26	70.00
2x16	17.78	39.52	2x50	60.96	82.70
2x20	22.86	44.60	2x60	73.66	95.40
2x24	27.94	49.68	2x64	78.74	100.48

X9555WW-2xXXA-PTV01	PBT UL 94V-0	Brass	Gold-Flash	X9555H
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生	日期
ΔX	日期
ΔX	日期
ΔX	日期
MARK	文件工程章

units:	mm
tolerance:	
X.X	±0.2mm
X.XX	±0.1mm
X.XXX	±0.05mm
UNSPECIFIED TOLERANCES	

DSND	DATE	SCALE: N/A	MODEL TYPE: Wire to board connector
DWN	DATE	VIEW:	PART NO.: 2.54mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.: X9555WW-2xXXA-PTV01
APPD	DATE	SIZE: A4	WEIGHT 1.0g
XKB INDUSTRIAL PRECISION CO., LIMITED			SHEET 1/1
			REVISION A0

DATE	SCALE: N/A	MODEL TYPE: Wire to board connector
DATE	VIEW:	PART NO.: 2.54mm Crimp Style Connectors
DATE	UNIT: mm/in	DWG NO.: X9555WW-2xXXA-PTV01
DATE	SIZE: A4	WEIGHT 1.0g
XKB INDUSTRIAL PRECISION CO., LIMITED		SHEET 1/1
		REVISION A0