

Technolo Request:

1.Outlook:

NO burr,no hurt.

2.Electronic performance:

a:Insulation resistance:

Above DC500V/100MΩ;

b:Endure voltage:


AC500V at 1 minute;

c:Contact resistance:

Under 30MΩ;

3.Insertion fore & withdrawal force;0.3-3kgf.

4.Salt spray test :24H.



	MATERIAL	PLATING
plastic	Pbt	Black
Waterproof tube	C3604	NI
terminal	Brass	NI
Spring	phosphor bronze	NI
silicone pad		

广东星坤科技股份有限公司

生 日期
發 日期

ΔX
MARK DESCRIPTION

REVISIONS

DATE REVISED APPROVED UNSPECIFIED TOLERANCES

ANGULAR ±5°
L ≤ 4 ±0.2
4 < L ≤ 16 ±0.3
16 < L ≤ 63 ±0.4
L > 63 ±0.5

DSND	DATE	SCALE: N/A	MODEL TYPE: DC-F0760
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
KKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT SHEET REVISION 1.0g 1/1 A0