



**Specifications:**

规格:  
 Voltage rating:250V AC/DC  
 额定电压: 250V AC/DC  
 Current rating:3A AC/DC  
 额定电流: 3A AC/DC  
 Withstanding voltage:1500V AC/minute  
 耐受电压:1500V AC/分钟  
 Temperature range:-25℃~+85℃  
 温度范围: -25℃~+85℃  
 Insulation resistance:≥1000MΩ  
 绝缘电阻: ≥1000MΩ  
 Contact resistance:≤20mΩ  
 接触电阻: ≤20mΩ  
 After environmental testing:≤30mΩ  
 环境测试后: ≤30兆欧  
 Max.Processing Temp:240℃ for30-60seconds  
 (260℃ for10seconds)

X9555 W V S-2xXX A-6T V01 XX

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- 1.Series No
- 2.Category:W-WAFER
- 3.Welding Board Angle:V-Straight 180°
- 4.Welding Way:S-SMT
- 5.Row No-Pin No:2xXX-2x06P-2x64P
- 6.Plug the Pin&Special NO:A-Ejector Header
- 7.Material:6T-PA6T 94V-0
- 8.Plating Category:V01-All Gold Flash
- 9.Color:Blank-Natural Color

poles	Dimensions(mm)		poles	Dimensions(mm)	
	A	B		A	B
2x06	5.08	26.82	2x26	30.48	52.22
2x08	7.60	29.36	2x30	35.56	57.30
2x10	10.16	31.90	2x34	40.64	62.38
2x14	15.24	36.98	2x40	48.26	70.00
2x16	17.78	39.52	2x50	60.96	82.70
2x20	22.86	44.60	2x60	73.66	95.40
2x24	27.94	49.68	2x64	78.74	100.48

X9555WVS-2xXXA-6TV01	LCP UL 94V-0	Brass	Gold-Flash	X9555H
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

PCB Hole Layout

生	日期
效	
ΔX	
ΔX	
ΔX	
MARK	文件工程章

DESCRIPTION	DATE	REVISED	APPROVED	units: mm
				tolerance:
				X.X ±0.2mm
				X.XX ±0.1mm
				X.XXX ±0.05mm
				UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A
DWN	DATE	VIEW:
CHKD	DATE	UNIT: mm/in
APPD	DATE	SIZE: A4
KKB INDUSTRIAL PRECISION CO., LIMITED		

MODEL TYPE: Wire to board connector		
PART NO.: 2.54mm Crimp Style Connectors		
DWG NO.: X9555WVS-2xXXA-6TV01		
WEIGHT	SHEET	REVISION
1.0g	1/1	A0