




XKB Connectivity



XKB Connectivity

NOTES:

1. ELECTRICAL
 - 1) VOLTAGE CURRENT RATING: 10AMP 30VAC
 - 2) INSULATION RESISTANCE: 100M MINI
 - 3) CONTACT RESISTANCE 50mQ MAXE
 - 4) WITHSTANDING VOLTAGE 300VAC
 - 5) OPERATING TEMPERATURE -55CT0+85C
2. Mechanical
 - 1) Mating Force 30N MAX
 - 2) Unmating Force 7N MIN.
3. DIMENSIONS MARKED "TO BE CHECKED BY QC & IPQC"
4. PART NO.



P.C.B LAYOUT

XKB Connectivity

XKB Connectivity

U213-05XN-4BH84

G: GREEN
B: BLACK
BL: BLUE

1: Au 1U"
5: Au 15U"
6: Au 30U"

1: PBT
2: PA6T
3: PA9T
4: LCP

					DSND		DATE		SCALE: N/A	MODEL TYPE: MINI USB	
					ANGLAR	±5°	DWN	DATE	VIEW:	PART NO.:	
Δx					L ≤ 4	±0.2	CHKD	DATE	UNIT: mm/in	DWG NO.:	
Δx					4 < L ≤ 16	±0.3	APPD	DATE	SIZE: A4	U213-05XN-4BH84	
Δx					16 < L ≤ 63	±0.4				REVISION	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5	XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g	
REVISIONS					UNSPECIFIED TOLERANCES						SHEET 1/1
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn											REVISION A0