



Recommended P.C.B. Layout
General Tolerance±0.05

Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥100MΩ
- Contact resistance: ≤30mΩ
- After environmental testing : ≤40mΩ

X1276 K V X-2*XX B-XX XX XX
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
- ② Category : K-Cowfish Longhorn Connector
- ③ Welding Board Angle: V- Straight 180°
- ④ Welding Way: Blank-DIP
- ⑤ Row No.-Pin No.: 2*XX-Double Row
- ⑥ Plug the Pin & Special No.: B-With Convex platform
- ⑦ Material : 6T-PA6T 94V-0
- ⑧ Plating Category: V01-All Gold Flash;
SN-Bright tin plating ;
- ⑨ Color: Blank-natural color

X1276KV-2*XXB-6T5N	PA6T UL 94V-0	Brass	Tin-plated	X1276Hl
X1276KV-2*XXB-6TV01			Gold-Flash	
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

广东星坤科技股份有限公司

生 日期
發 日期

ΔX
MARK

文件工程章

REVISIONS

www.xk-lg.cn www.helloxkb.com www.helloxkb.cn

ANGULAR ±5°
L ≤ 4 ±0.2
4 < L ≤ 16 ±0.3
16 < L ≤ 63 ±0.4
L > 63 ±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X1276KV-2*XXB-6TXXX
DWN	DATE	VIEW:	PART NO.: 1.27mm Crimp Style Connector
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
KKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0