





Without CAP



P.C.B LAYOUT(R2)



P.C.B LAYOUT(R1)

Specifications:

- 1.Voltage rating:250VAC/DC
- 2.Current rating:1A AC/DC
- 3.Withstanding voltage:300V AC/minute
- 4.Temperature range:-40℃to+105℃
- 5.Insulation resistance:≥500MΩ Min
- 6.Contanct resistance:≤20MΩ Max
- 7.Material:PA6T 94V-0
- 8.Planting Category:1U"Gold
- 9.Reflow Soldering temperature:260±5℃, 10S

X1311 F V S -XX-C43-D35-X

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series NO.
- ② Category:F-Female
- ③ Welding Board Angle:V-Right Angle 90°
- ④ Welding Way:S-SMT
- ⑤ Row No-Pin No:xx-01p-40p
- ⑥ Plastic height:C=4.3mm
- ⑦ Plastic height:D=3.5mm
- ⑧ X:R1,R2

| | | | | |
|-----------------------|------------|--------------------|------------------|-----------------------|
| X1311FVS-XX-C43-D35-X | PA6T 94V-0 | Brass | 1U" Gold | X1311W |
| PART NO | Material | Material(Terminal) | Finish(Terminal) | Suitable XKB Terminal |

广东星坤科技股份有限公司

生效

| | |
|------|-------------|
| ΔX | 日期 |
| ΔX | 日期 |
| ΔX | 日期 |
| MARK | DESCRIPTION |

REVISIONS

UNSPECIFIED TOLERANCES

| | | | |
|---------------------------------------|-------|-------------|-----------------------|
| DSND | DATE | SCALE: N/A | MODEL TYPE: |
| DWN | DATE | VIEW: | X1311FVS-XX-C43-D35-X |
| CHKD | DATE | UNIT: mm/in | PART NO.: |
| APPD | DATE | SIZE: A4 | DWG NO.: |
| XKB INDUSTRIAL PRECISION CO., LIMITED | | | X1311FVS-XX-C43-D35-X |
| WEIGHT | SHEET | REVISION | |
| 1.0g | 1/1 | A0 | |

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn