



PCB LAYOUT

XKB Connectivity

XKB Connectivity

■ 规格 Specifications:

- 额定电压 Voltage rating: 250VAC/DC。
- 额定电流 Current rating: 1A AC/DC
- 耐电压 Withstanding voltage: 300V AC/minute
- 温度区间 Temperature range: -40°C to +105°C
- 绝缘电阻 Insulation resistance: ≥500MΩ Min
- 接触电阻 Contact resistance: ≤20MΩ Max
- 材料 Material: PA6T 94V-0
- 镀层 Plating Category: 1U"Gold
- 波峰焊温度 Wave soldering temperature: 255±5°C, 10s

XKB Connectivity

X1311 WR-XX J- C26 D40

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category: W-Wafer
- ③ Welding Board Angle: R-Stright 90°
- ④ Row No -Pin No: XX-01P-40P
- ⑤ Plastic height: J=1.0mm
- ⑥ Plastic length: C=2.6mm
- ⑦ Plastic length: C=4.0mm

XKB Connectivity

X1311WR-XXJ-C26D40	PA6T 94V-0	Brass	1U"Gold	X1311F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生
發

日
期

文件工程章

REVISIONS

www.xkb.cn www.helloxkb.com www.helloxkb.cn

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X1311WR-XXJ-C26D40
DWNN	DATE	VIEW:	PART NO.: 1.27mm Crimp Style Connector
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0