



Specifications:

- 1.Voltage rating:250VAC/DC
- 2.Current rating:1A AC/DC
- 3.Withstanding voltage:300V AC/minute
- 4.Temperature range:-40℃to+105℃
- 5.Insulation resistance:≥500MΩ Min
- 6.Contanct resistance:≤20MΩ Max
- 7.Material:PA6T 94V-0
- 8.Planting Category:1U"Gold
- 9.Reflow Soldering temperature:260±5℃. 10S
- 10.Operating Category:-40℃ to+105℃

X1311 W V S -XX J-C18 D42-X
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series NO.
- ② Category:W-wafer
- ③ Welding Board Angle:V-Straight 90°
- ④ S-SMT
- ⑤ Row No-Pin No:xx-01p-40p
- ⑥ Plastic height:J=1.0mm
- ⑦ Pin height:C=1.8mm
- ⑧ Pin height:D=4.2mm
- ⑨ X:R1,R2

X1311WVS-XXJ-C18D42-X	PA6T 94V-0	Brass	1U" Gold	X1311F
PART NO	Material	Material(Terminal)	Finish(Terminal)	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

文件工程章

REVISIONS

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	X1311WVS-XXJ-C18D42-X
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			X1311WVS-XXJ-C18D42-X
WEIGHT	SHEET	REVISION	
1.0g	1/1	A0	