



PCB LAYOUT

规格 Specifications:

- 额定电压 Voltage rating: 250VAC/DC。
- 额定电流 Current rating: 1A AC/DC
- 耐电压 Withstanding voltage: 300V AC/minute
- 温度区间 Temperature range: -40°C to +105°C
- 绝缘电阻 Insulation resistance: ≥500MΩ Min
- 接触电阻 Contact resistance: ≤20MΩ Max
- 材料 Material: PA6T 94V-0
- 镀层 Plating Category: 1U"Gold
- 波峰焊温度 Wave soldering temperature: 255±5°C, 10s

X1311 F R- XX - C43 D24

① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category: F-Female
- ③ Welding Board Angle: R-Straight 90°
- ④ Row No -Pin No: XX-01P-40P
- ⑤ Plastic height: C=4.3mm
- ⑥ Plastic length: D=2.4mm

| | | | | |
|-------------------|------------|---------------|-------------|-----------------------|
| X1311FR-XX-C43D24 | PA6T 94V-0 | Brass | 1U"Gold | X1311W |
| PART NO | Material | Material(Pin) | Finish(Pin) | Suitable XKB Terminal |

广东星坤科技股份有限公司

XKB Connectivity

生 日期

文件工程章

| | | | | |
|-----------|------|---------|----------|------------------------|
| REVISIONS | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
| | | | | |
| | | | | |
| | | | | |
| | | | | |

| | | | |
|---------------------------------------|------|-------------|--|
| DSND | DATE | SCALE: N/A | MODEL TYPE: X1311FR-XX-C43D24 |
| DWN | DATE | VIEW: | PART NO.: 1.27mm Crimp Style Connector |
| CHKD | DATE | UNIT: mm/in | DWG NO.: |
| APPD | DATE | SIZE: A4 | |
| XKB INDUSTRIAL PRECISION CO., LIMITED | | | WEIGHT: 1.0g |
| | | | SHEET: 1/1 |
| | | | REVISION: A0 |