



PCB LAYOUT

XKB Connectivity

■ 规格 Specifications:

- 额定电压 Voltage rating: 250VAC/DC。
- 额定电流 Current rating: 1A AC/DC
- 耐电压 Withstanding voltage: 300V AC/minute
- 温度区间 Temperature range: -40°C to +105°C
- 绝缘电阻 Insulation resistance: ≥500MΩ Min
- 接触电阻 Contact resistance: ≤20MΩ Max
- 材料 Material: PA6T 94V-0
- 镀层 Plating Category: 1U"Gold
- 波峰焊温度 Wave soldering temperature: 255±5°C, 10s

X1311 W V-XX J- C18 D27

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category: W-Wafer
- ③ Welding Board Angle: V-Stright 180°
- ④ Row No -Pin No: XX-01P-40P
- ⑤ Plastic height: J=1.0mm
- ⑥ Plastic length: C=2.7mm
- ⑦ Plastic length: D=1.8mm

X1311WV-XXJ-C18D27	PA6T 94V-0	Brass	1U"Gold	X1311F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	DESCRIPTION

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X1311WV-XXJ-C18D27
DWNN	DATE	VIEW:	PART NO.: 1.27mm Crimp Style Connector
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0