


Specifications:


- 1.Voltage rating:250VAC/DC
- 2.Current rating:1A AC/DC
- 3.Withstanding voltage:300V AC/minute
- 4.Temperature range:-40℃to+105℃
- 5.Insulation resistance:≥500MΩ Min
- 6.Contanct resistance:≤20MΩ Max
- 7.Material:PA6T 94V-0
- 8.Planting Category:1U"Gold
- 9.Reflow Soldering temperature:260±5℃, 10S



X1321 F V -2*XX-C43-D24

① ② ③ ④ ⑤ ⑥

- ① Series NO.
- ② Category:F-Female
- ③ Welding Board Angle:V-Right Angle 180°
- ④ Row No-Pin No:xx-2*01p-40p
- ⑤ Plastic height:C=4.3mm
- ⑥ Plastic height:D=2.4mm



P.C.B LAYOUT

X1321FV-2*XX-C43D24	PA6T 94V-0	Brass	1U" Gold	X1321W
PART NO	Material	Material(Terminal)	Finish(Terminal)	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

REVISIONS

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	X1321FV-2*XX-C43D24
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.:
			X1321FV-2*XX-C43D24
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT
			1.0g
			SHEET
			1/1
			REVISION
			A0

文件工程章