



Specifications:

- 1.Voltage rating:250VAC/DC
- 2.Current rating:1A AC/DC
- 3.Withstanding voltage:1000V AC/minute
- 4.Temperature range:-40℃ to+105℃
- 5.Insulation resistance:≥500MΩ Min
- 6.Contanct resistance:≤20MΩ Max
- 7.Material:PA6T 94V-0
- 8.Planting Category:1U"Gold
- 9.Reflow Soldering temperature:260±5℃, 10S
- 10.Operating Category:-40℃ to+105℃

X1321 W V -2*XX J-C30-D23

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Category:W-wafer
- ③ Welding Board Angle:V-Stright 180°
- ④ Row No-Pin No:2*xx-01p-40p
- ⑤ Plastic height:J=1.0mm
- ⑥ Pin height:C=3.0mm
- ⑦ Pin height:D=2.3mm

X1321WV-2*XXJ-C30D23	PA6T 94V-0	Brass	1U" Gold	X1321F
PART NO	Material	Material(Terminal)	Finish(Terminal)	Suitable XKB Terminal

广东星坤科技股份有限公司

生效	ΔX	日期	日期	日期	日期
	ΔX				
	ΔX				
	MARK				

文件工程章

DSND	DATE	SCALE: N/A	MODEL TYPE: X1321WV-2*XXJ-C30D23
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	X1321WV-2*XXJ-C30D23
UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO., LIMITED
			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0

REVISIONS
www.helloxkb.com www.helloxkb.cn