



Specifications:

1. Voltage rating: 250VAC/DC
2. Current rating: 1A AC/DC
3. Withstanding voltage: 1000V AC/minute
4. Temperature range: -40°C to +105°C
5. Insulation resistance: ≥ 500MΩ Min
6. Contact resistance: ≤ 20MΩ Max
7. Material: PA6T 94V-0
8. Plating Category: 1U" Gold
9. Reflow Soldering temperature: 260 ± 5°C, 10S
10. Operating Category: -40°C to +105°C

X1321 WR -2*XX J-C40-D18

- ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Category: W-wafer
- ③ Welding Board Angle: R-Right Angle 90°
- ④ Row No-Pin No: 2*xx-01p-40p
- ⑤ Plastic height: J=1.0mm
- ⑥ Pin height: C=4.0mm
- ⑦ Pin height: D=1.8mm

X1321WR-2*XXJ-C40D18	PA6T 94V-0	Brass	1U" Gold	X1321F
PART NO	Material	Material(Terminal)	Finish(Terminal)	Suitable XKB Terminal

P.C.B LAYOUT

广东星坤科技股份有限公司

生效

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

REVISIONS

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

文件工程章

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	X1321WR-2*XXJ-C40D18
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			X1321FVS-2*XXJ-C43D48
WEIGHT	SHEET	REVISION	
1.0g	1/1	A0	

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES