



P.C.B LAYOUT

No.of Positions	A(mm)
2*02~2*15P	0.10
2*16~2*30P	0.15
2*31~2*40P	0.20
2*41~2*50P	0.25

Specifications:

- 1.Voltage rating:250VAC/DC
- 2.Current rating:1A AC/DC
- 3.Withstanding voltage:300V AC/minute
- 4.Temperature range:-40℃ to+105℃
- 5.Insulation resistance:≥500MΩ Min
- 6.Contanct resistance:≤20MΩ Max
- 7.Material:PA6T 94V-0
- 8.Planting Category:1U"Gold
- 9.Reflow Soldering temperature:260±5℃, 10S
- 10.Operating Category:-40℃ to+105℃

X1321 W V S -2*XX J-C40 D53

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series NO.
- ② Category:W-wafer
- ③ Welding Board Angle:V-Stright 90°
- ④ S-SMT
- ⑤ Row No-Pin No:xx-2*01p-40p
- ⑥ Plastic height:J=1.0mm
- ⑦ Pin height:C=4.0mm
- ⑧ Pin height:D=5.3mm

X1321WVS-2*XXJ-C40D53	PA6T 94V-0	Brass	1U" Gold	X1321F
PART NO	Material	Material(Terminal)	Finish(Terminal)	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

MARK	DESCRIPTION	DATE	REVISIONS
ΔX			
ΔX			
ΔX			

DESCRIPTION

REVISIONS

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

文件工程章

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	X1321WVS-2*XXJ-C40D53
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			X1321WVS-2*XXJ-C40D53
WEIGHT	SHEET	REVISION	
1.0g	1/1	A0	