



**Specifications:**

规格:  
**Voltage rating:**150V AC/DC  
 额定电压: 150V AC/DC  
**Current rating:**3A AC/DC  
 额定电流: 3A AC/DC  
**Withstanding voltage:**500V AC/minute  
 耐受电压: 500V AC/分钟  
**Temperature range:**-25°C~+85°C  
 温度范围: -25°C~+85°C  
**Insulation resistance:**≥1000MΩ  
 绝缘电阻: ≥1000MΩ  
**Contact resistance:**≤20mΩ  
 接触电阻: ≤20mΩ  
**After environmental testing:**≤40mΩ  
 环境测试后: ≤40兆欧

**X1503 H-XX-N0**

① ② ③ ④

1. Series No.
2. Category: H-HSG
3. Row No-Pin No: XX-04P~12P
4. Material: N0-PA66 94V-0

Poles	Dimensions(mm)			
	A	B	C	D
02		6.95	5.95	5.55
03	3.00	8.45	7.45	7.05
04	4.50	9.95	8.95	8.55
05	6.00	11.45	10.45	10.05
06	7.50	12.95	11.95	11.55
07	9.00	14.45	13.45	13.05
08	10.50	15.95	14.95	14.55
09	12.00	17.45	16.45	16.05
10	13.50	18.95	17.95	17.55
11	15.00	20.45	19.45	19.05
12	16.50	21.95	20.95	20.55

X1503H-XX-N0	PA66 UL 94V-0	X1503T	X1503W
PART NO	Material	Suitable Terminal	Suitable XKB

广东星坤科技股份有限公司

生	日期						units: mm
效							tolerance:
ΔX							X.X ±0.2mm
ΔX							X.XX ±0.1mm
MARK							X.XXX ±0.05mm
文件工程章							UNSPECIFIED TOLERANCES
DESCRIPTION		DATE	REVISED	APPROVED			
REVISIONS							
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn							

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector	
DWN		DATE		VIEW:	PART NO.:	
CHKD		DATE		UNIT: mm/in	1.50mm Crimp Style Connectors	
APPD		DATE		SIZE: A4	DWG NO.: X1503H-XX-N0	
KKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET	REVISION
				1.0g	1/1	A0