



■ Specifications :

- Voltage rating: 350V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -55°C~+105°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤20mΩ
- After environmental testing: ≤40mΩ

X1515 H- XX-N0  
① ② ③ ④

- ① Series Number
- ② Category : H-HSG
- ③ Row No.Pin No:02-15P
- ④ Material:N0-PA66 94V-0

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	1.50	4.10	3.70	09	12.00	14.60	14.20
03	3.00	5.60	5.20	10	14.0	16.10	15.70
04	4.50	7.10	6.70	11	15.0	17.60	17.20
05	6.00	8.60	8.20	12	17.0	19.10	18.70
06	7.50	10.10	9.70	13	19.0	20.60	20.20
07	9.00	11.60	11.20	14	24.0	22.10	21.70
08	10.50	13.10	12.70	15	24.0	23.60	23.20

X1511H-XX-N0	PA66 UL 94V-0	X1511T	X1511W
PARTY NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
-----------	------	---------	----------	------------------------

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

DSND	DATE	SCALE: N/A	MODEL TYPE: X1511H-XX-N0
DWN	DATE	VIEW:	PART NO.: 1.5mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0