



■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤10mΩ
- After environmental testing: ≤20mΩ

X2000 H- XX-N0

① ② ③ ④

- ① Series Number
- ② Category : H-HSG
- ③ Row No.Pin No:xx-02-16P
- ④ Material:N0-PA66;

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	4.43	6.10	10	18.00	20.34	22.10
03	4.00	6.34	8.10	11	20.00	22.34	24.10
04	6.00	8.34	10.10	12	22.00	24.34	26.10
05	8.00	10.34	12.10	13	24.00	26.34	28.10
06	10.00	12.34	14.10	14	26.00	28.34	30.10
07	12.00	14.34	16.10	15	28.00	30.34	32.10
08	14.00	16.34	18.10	16	30.00	32.34	34.10
09	16.00	18.34	20.10				

X2000H-XX-N0	PA66 UL 94V-0	X2000T	X2000W
PARY NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

ΔX	日期
MARK	DESCRIPTION

文件工程章

REVISIONS

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X2000H-XX-N0
DWN	DATE	VIEW:	PART NO.: 2.0mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0