



Specifications:

规格:
 Voltage rating: 250V AC/DC
 额定电压: 250V AC/DC
 Current rating: 3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage: 800V AC/minute
 耐受电压: 800V AC/分钟
 Temperature range: -25°C~+85°C
 温度范围: -25°C~+85°C
 Insulation resistance: ≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance: ≤10mΩ
 接触电阻: ≤10mΩ
 After environmental testing: ≤20mΩ
 环境测试后: ≤20mΩ



X2026 H X-2xXX AH-N0 XX

① ② ③ ④ ⑤ ⑥ ⑦

1. Series No
2. Category: H-HSG
3. Appearance type: Blank-Ordinary
4. Row No-Pin No: 2xXX-2x02P~2x22P
5. Plug the Pin&Special NO:
A-With Lock; H-High Salient Point
6. Material: N0-PA66 94V-0
7. Color: Blank-Natural Color



poles	Dimensions(mm)			poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2x02	2.00	9.00	4.50	2x09	16.00	23.00	18.50	2x16	30.00	37.00	32.50
2x03	4.00	11.00	6.50	2x10	18.00	25.00	20.50	2x17	32.00	39.00	34.50
2x04	6.00	13.00	8.50	2x11	20.00	27.00	22.50	2x18	34.00	41.00	36.50
2x05	8.00	15.00	10.50	2x12	22.00	29.00	24.50	2x19	36.00	43.00	38.50
2x06	10.00	17.00	12.50	2x13	24.00	31.00	26.50	2x20	38.00	45.00	40.50
2x07	12.00	19.00	14.50	2x14	26.00	33.00	28.50				
2x08	14.00	21.00	16.50	2x15	28.00	35.00	30.50				



B-B

X2026H-2xXXAH-N0	Nylon 66 UL 94V-0	X2026T	X2026VW-A, X2026WR-A
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

生效	日期
ΔX	ΔX
ΔX	ΔX
MARK	文件工程章

DATE	REVISED	APPROVED	units:	mm
			tolerance:	
			X.X	±0.2mm
			X.XX	±0.1mm
			X.XXX	±0.05mm
				UNSPECIFIED TOLERANCES

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	2.00mm Crimp Style Connectors
APPD		DATE		SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED					X2026H-2xXXAH-N0
		WEIGHT	SHEET	REVISION	
		1.0g	1/1	A0	