



Specifications:

规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage:1000V AC/minute
 耐受电压: 1000V AC/分钟
 Temperature range:-25℃~+85℃
 温度范围: -25℃~+85℃
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance:≤30mΩ
 接触电阻: ≤30mΩ
 After environmental testing:≤50mΩ
 环境测试后: ≤50兆欧

X2026 H X- 2xXX D-N0 XX

① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:H-HSG
- 3.Appearance type:Blank-Ordinary
- 4.Row No-Pin No:2xXX-2x02P~2x16P
- 5.Plug the Pin&Special N0:
D-With Lock in the middle
- 6.Material:N0-PA66 94V-0
- 7.Color:Blank-Natural Color

poles	Dimensions(mm)			poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2x02	2.00	4.60	6.76	2x10	18.00	20.60	22.76	2x18	34.00	36.60	38.76
2x03	4.00	6.60	8.76	2x11	20.00	22.60	24.76	2x19	36.00	38.60	40.76
2x04	6.00	8.60	10.76	2x12	22.00	24.60	26.76	2x20	38.00	40.60	42.76
2x05	8.00	10.60	12.76	2x13	24.00	26.60	28.76				
2x06	10.00	12.60	14.76	2x14	26.00	28.60	30.76				
2x07	12.00	14.60	16.76	2x15	28.00	30.60	32.76				
2x08	14.00	16.60	18.76	2x16	30.00	32.60	34.76				
2x09	16.00	18.60	20.76	2x17	32.00	34.60	36.76				

X2026H-2xXXD-N0	Nylon 66 UL 94-V0	X2026T-D	X2026H-D
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

生效	日期
文件	工程章

DATE	REVISED	APPROVED	units:	mm
			tolerance:	
			X.X	±0.2mm
			X.XX	±0.1mm
			X.XXX	±0.05mm
UNSPECIFIED TOLERANCES				

DSND	DATE	SCALE: N/A	MODEL TYPE: Wire to board connector
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	2.00mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.: X2026H-2xXXD-N0
KKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0