

**Specifications:**

规格:  
 Voltage rating:250V AC/DC  
 额定电压: 250V AC/DC  
 Current rating:3A AC/DC  
 额定电流: 3A AC/DC  
 Withstanding voltage:800V AC/minute  
 耐受电压: 800V AC/分钟  
 Temperature range:-25℃~+85℃  
 温度范围: -25℃~+85℃  
 Insulation resistance:≥1000MΩ  
 绝缘电阻: ≥1000MΩ  
 Contact resistance:≤10mΩ  
 接触电阻: ≤10mΩ  
 After environmental testing:≤20mΩ  
 环境测试后: ≤20兆欧


**X2026 H X- 2xXX HF-N0 XX**

① ②③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:H-HSG
- 3.Appearance type:Blank-Ordinary
- 4.Row No-Pin No:2xXX-2x02P~2x22P
- 5.Plug the Pin&special No:  
HF-Halogen Free
- 6.Material:NO-PA66 94V-0
- 7.Color:Blank-Natural Color  
BK-Black

poles	Dimensions(mm)			poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2x02	2.00	5.90	4.50	2x09	16.00	19.90	18.50	2x16	30.00	33.90	32.50
2x03	4.00	7.90	6.50	2x10	18.00	21.90	20.50	2x17	32.00	35.90	34.50
2x04	6.00	9.90	8.50	2x11	20.00	23.90	22.50	2x18	34.00	37.90	36.50
2x05	8.00	11.90	10.50	2x12	22.00	25.90	24.50	2x19	36.00	39.90	38.50
2x06	10.00	13.90	12.50	2x13	24.00	27.90	26.50	2x20	38.00	41.90	40.50
2x07	12.00	15.90	14.50	2x14	26.00	29.90	28.50	2x21	40.00	43.90	42.50
2x08	14.00	17.90	16.50	2x15	28.00	31.90	30.50	2x22	42.00	45.90	44.50

X2026H-2xXX-N0BK	Nylon 66 UL 94V-0 Black	X2026T	X2026W
X2026H-2xXXHF-N0	Nylon 66 UL 94V-0 Halogen Free		
X2026H-2xXX-N0	Nylon 66 UL 94V-0		
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal



广东星坤科技股份有限公司

生	日期	units:	mm
ΔX		tolerance:	
ΔX		X.X	±0.2mm
ΔX		X.XX	±0.1mm
MARK		X.XXX	±0.05mm
UNSPECIFIED TOLERANCES			

DSND	DATE	SCALE: N/A	MODEL TYPE: Wire to board connector
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	2.00mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
			X2026H-2xXXXX-N0
XKB INDUSTRIAL DECISION CO. LIMITED			WEIGHT   SHEET   REVISION

生	日期	DESCRIPTION	DATE	REVISED	APPROVED	REVISIONS
敬		文件工程章				