



PCB
PCBLAYOUT

Specifications:

规格:
Voltage rating: 250V AC/DC
额定电压: 250V AC/DC
Current rating: 3A AC / DC
额定电流: 3A AC / DC
Withstanding voltage: 1000V AC/minute
耐压电压: 1000V AC/minute
Temperature range: -25°C ~ +85°C
温度范围: -25°C ~ +85°C
Insulation resistance: ≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance: ≤10mΩ
接触电阻: ≤10mΩ
After environment testing: ≤20mΩ
环境试验后: ≤20mΩ

X2510 W V - XX - N0 SN

① ②③ ④ ⑤ ⑥

- ① Series No.
- ② Category: W-WAFER
- ③ Welding Board Angle: V-180°
- ④ Row No.-Pin No. XX-Single Row
- ⑤ Material: N0-PA66 94V-0
- ⑥ Planting Category SN-Bright Tin Plating

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	2.54	5.08	10	22.86	25.4
3	5.08	7.62	11	25.4	27.94
4	7.62	10.16	12	27.94	30.48
5	10.16	12.70	13	30.48	33.02
6	12.70	15.24	14	33.02	35.56
7	15.24	17.78	15	35.56	38.10
8	17.78	20.32			
9	20.32	22.86			

X2510WV-XX-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X2510H
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

REVISIONS					UNSPECIFIED TOLERANCES	DSND	DATE	SCALE: N/A	MODEL TYPE:		
ΔX					ANGULAR						
ΔX					L ≤ 4			VIEW:	PART NO.:		
ΔX					4 < L ≤ 16			UNIT: mm/in	2.54 mm Crimp Style Connectors		
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63			SIZE: A4	DWG NO.:		
					L > 63				X2510WV-XX-N0SN		
					KKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn									1.0g	1/1	A0